Semi-Crystalline Products



Case Study

Highly reinforced polyamide 6 as an alternative to steel, aluminum and GMT





Figure 1 Injection-molded spare wheel recess with a bodywork-reinforcing effect

Its outstanding stiffness and strength opens the door to new applications in automotive engineering for highly reinforced polyamide 6 as an alternative to sheet steel, aluminum and glass-mat-reinforced thermoplastics (GMT). One current example is the spare wheel recess with integrated reinforcing channels in the new Audi A8. The recess is made of Durethan® DP BKV 60 H2.0 EF, a highly filled polyamide 6 from LANXESS with 60 % glass fibers. This polyamide 6 is the material of choice because it enables precise injection molding of the part's complex geometry. It would be very difficult to make the component from sheet metal due to the limited space available and the high draw ratios. This plastic also enables direct integration of numerous functions. Incorporating these functions in a metal design would have required a large number of separate production and assembly steps with all the associated costs. One of the reasons for deciding against a GMT design was the huge amount of reworking the finely structured component would have required. The spare wheel recess is made by

OEM: Audi

Grade: Durethan® DP BKV 60 H2.0 EF

Manufacturer: voestalpine Plastics

<u>voestalpine Plastics</u>, a company based in the Dutch town of Putte.

With dimensions of $100 \times 85 \times 32$ cm, the spare wheel recess is unusually large for an injection-molded part. The plastic alone weighs approximately nine kilograms. The component is bonded and bolted to the body framework, and fulfils the additional function of reinforcing the rear end of the car. This is achieved by integrating two reinforcing channels, each around two meters long, using gas injection technology (GIT).



Figure 2 reverse side of spare wheel with integrated reinforcing channels



The plastic makes a major contribution to the high overall stiffness. Its tensile modulus of approximately 19,000 MPa at ambient temperature (conditioned: 13,000 MPa) is twice as high as that of a standard polyamide 6 filled with 30 % glass fibers. It also retains its stiffness at high temperatures – as required by Audi for components located close to the exhaust system, for example. This outstanding stiffness and strength are also important because the recess supports numerous fittings and attachments weighing a total of around 70 kg. These include the spare wheel, air spring compressor, vehicle jack, tools, battery and various control units. The battery is attached to an aluminum sheet that is integrated in the component. This stops it from becoming detached in the event of a rear-end collision.

The spare wheel recess is made in a single-stage injection-molding process. Particular challenges include the size and 3D complexity of the molded part, the high shot weight of around 12 kg, precise back-injection of the aluminum sheet for the battery and integration of the GIT process for the reinforcing channels. Precise metering is achieved using a 2,700 metric ton injection molding machine with a screw that has a relatively large diameter of 150 mm.

First of all, the polyamide 6 is injected into the mold. The highly reinforced thermoplastic's excellent flowability – similar to that of a standard polyamide 6 with 30 % glass fibers – means that only two gates are required. The GIT process is then used to produce the reinforcing channels, the excess melt being forced into overflow cavities. Durethan® BKV 60 H2.0 EF makes thin walls possible. In addition, the expelled melt can be returned to the process as recyclate at a ratio of 30 %. Another key benefit of the polyamide 6 is the fact that its impressive flowability results in mold wear comparable to that observed when using a standard polyamide 6 with 30 % glass fibers.

LANXESS provided a comprehensive range of services during the development of the spare wheel recess. This includes using mold flow analyses to optimize wall thicknesses and minimize distortion. LANXESS also helped with mold construction, mold proving and initial production trials. Moreover, the GIT material's recyclability was tested and integrative simulation was used to calculate the molded part's vibration characteristics.

This information and our technical advice - whether verbal, in writing or by way of trials - are given in good faith but without warranty, and this also applies where proprietary rights of third parties are involved. Our advice does not release you from the obligation to verify the information currently provided - especially that contained in our safety data and technical information sheets - and to test our products as to their suitability for the intended processes and uses. The application, use and processing of our products and the products manufactured by you on the basis of our technical advice are beyond our control and, therefore, entirely your own responsibility. Our products are sold in accordance with the current version of our General Conditions of Sale and Delivery.

Trial Products (grade designations beginning with the codes DP, TP, KL or KU)

This is a Sales Product at the developmental stage (a Trial Product). For this reason, no assurances can be given as to type conformity, processability, long-term performance characteristics or other production or application parameters. No definitive statements can be made regarding the behavior of the product during processing or use. The purchaser/user uses the product entirely at his own risk. The marketing and continued supply of this material are not assured and may be discontinued at any time.

X

Page 2 of 2 | Edition 14.06.2010 | CS TI 2010-001 EN